



FEATURES

- Clear & informative graphic display
- Highest grade HEPA and carbon technology
- Automatic electronic flow control - maintains a constant extraction rate even as the filter blocks
- Gas and particle sensors to warn the operator
- Up to 2 large hoods

SPECIFICATIONS

Voltage	120v	230v
Part Number	080470D	080465D
Wattage	0.36kW	0.36kW
Frequency	50Hz / 60Hz	50Hz / 60Hz
Cabinet Height	720mm	720mm
Cabinet Width	445mm	455mm
Cabinet Depth	610mm	610mm
Cabinet Weight	55kg	55kg
Sound Level	<60dBa	<60dBa
Airflow	645m3/h	645m3/h

INCLUDED AS STANDARD...

FILTERS



Main Filter
Code
113505

Description
HEPA/Chemical



Pre-filter
Code
200025

Description
F5 Pad

Find out more:



www.purexusa.com



sales@purexusa.com



+1 336 288 1613

CONNECTION KIT

Connection kit is included
see overleaf for options

*Machine Supplied With • 1 x Main Filter • 1 x Pre-filter •
1 x Connection Kit • 1 x Power Cable • 1 x Manual*

OPTIONS

Main Filter

Code:	Description:
113505H	HEPA/Chemical (Hydrophobic)
113579	HEPA/Twin Chemical
113668	HEPA/Twin Chemical
113512	HEPA/Chemical (Cleanroom)
113669	HEPA/Chemical (Cleanroom)
113508	Chemical
113809	HEPA
113513	Solvent Lock

Main Filter

Code:	Description:
113662	Chemical Special
113505P	Chemical Special
113531	Pleated Bag

Connection Kits

Included



The 650 machine is suitable for either single arm or dual arm.

The machine is high in mobility due to its castors and the multi position arm; meaning the machine can be moved from station to station as and when required.

The large hood area of 420mm x 320mm gives the operator ample space to work.

Optional Extra

Upgrade your 650 machine with an additional arm!

Code:
120197



With its high stability triple axis, the additional arm can be used for an extra workstation. This allows more technicians to work at any one time!

Interfacing



Interfacing can remotely start the Purex machine when the connected machine starts.

Interfacing can also warn the connected machine when the Purex machine is in alarm.

Take a look through our Interfacing Guide to see our extensive range of options



Tel: (336) 288-1613 | eMail: sales@purexusa.com

www.sales@purexusa.com
tel:(336) 288-1613
3714 Alliance Dr, Ste. 100
Greensboro
NC 27407